Rittal – The System.

Faster – better – everywhere.





AS 4050.437 Support rail cutter MC3

State: 07.12.2025 (Source: rittal.com/ua-en)



AS 4050.437 - Support rail cutter MC3

Manual profile cutter for cutting C rails 30/15 and support rails TS 35/7.5 and TS 35/15 to length, burr-free. The desired rail length can be set precisely and reproducibly using the ruler (mm/inch) and the adjustable end stop. For mounting on the workbench.



Features

Model No.	AS 4050.437
Product description	Manual profile cutter for cutting C rails 30/15 and support rails TS 35/7.5 and TS 35/15 to length, burr-free. The desired rail length is set precisely and reproducibly using the ruler (mm/inch) and the adjustable end stop. For mounting on the workbench.
Benefits	Inexpensive manual cutting of mounting angles and support rails Easier to cut mounting angles and support rails to the correct length than sawing by hand Burr-free cutting to length with eccentric lever, no major force required Low-maintenance and with a long service life
Support area	Width: 1,343 mm Height: 1,162 mm Depth: 312 mm
Machinable material	Sheet steel Aluminium Copper
Packs of	1 pc(s).
Net weight	15
Gross weight	16.15
Customs tariff number	73269098

© Rittal 2025 2

Features

EAN	4028177954021
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890

© Rittal 2025 3