

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.565 Cutting Terminal CT

State: 18.04.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.565 - Cutting Terminal CT

Cut wiring ducts, cable duct covers and support rails to the precise required length with our Cutting Terminal CT cutting centre. Designed specifically for one-off and small-scale manufacturing.



## Features

|                     |   |
|---------------------|---|
| Model No.           | AS 4050.565   |
| Design              | Modern operating solution with 21.5" full-HD multitouch monitor, Terra mini-PC with i5 processor<br>For support rails including punching function for slots and transverse holes<br>Five DIN rail sizes in one template<br>US version<br>Cutting Terminal CT H  |
| Benefits            | Fast, precise, reliable working<br>Easy to use<br>User-friendly, reliable operation<br>High-performance tools mean clean cuts and no swarf production<br>Significant time savings compared to manual cutting<br>Very low costs for cutting waste thanks to optimisation of the cutting process<br>Automatic retraction of the end stop during the cutting process |
| Supply includes     | Cutting Terminal CT H<br>Operating unit   |
| Machinable material | Steel<br>Aluminium<br>Copper<br>Plastic   |

# Features

|                                      |  |
|--------------------------------------|--|
| Machine options                      | Label printer 4050.557<br>Support system 4050.558  |
| Interfaces                           | Data imports from Eplan Pro Panel via the RiPanel Processing Center<br>Data import of CSV lists  |
| Note                                 | We reserve the right to make technical modifications   |
| Support area                         | Width: 4,000 mm<br>Height: 1,850 mm<br>Depth: 673 mm   |
| Max. machinable height of cable duct | 100 mm   |
| Max. machinable width of cable duct  | 125 mm   |
| Control voltage (DC)                 | 24 V   |
| Rated operating voltage              | 230 V, 1~, 60 Hz   |
| Support rail type                    | Top-hat rails 15 (to EN 60 715)<br>Top-hat rails 35/15 (to EN 60 715)<br>Top-hat rails 35/7.5 (to EN 60 715)<br>Busbars NLS-CU 3/10<br>C rails 34 x 15 (to EN 60715) |
| For wall thickness (max.)            | 2.5 mm   |
| Packs of                             | 1 pc(s).   |
| Net weight                           | 270 kg   |
| Gross weight                         | 300 kg   |
| Customs tariff number                | 84571090   |