

# Rittal – The System.

Faster – better – everywhere.



## VX 5301.518 Castor module

State: 08.07.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5301.518 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | VX 5301.518   |
| Supply includes       | 1 transport module with 2 castors<br>1 transport module with 2 castors, fixed<br>Assembly parts                                 |
| Dimensions            | Width: 756 mm<br>Height: 82.5 mm<br>Depth: 79 mm  |
| Assembly instruction  | The base area must be open at the mounting points   |
| To fit                | Enclosure type: VX: = 800 mm<br>Enclosure type: VX IT   |
| Load capacity         | Max. admissible load: Static 15,000 N<br>Max. admissible load: Dynamic 10,000 N   |
| Note                  | The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground.                                  |
| Packs of              | 1 pc(s).  |
| Net weight            | 11.5 kg   |
| Gross weight          | 12.12 kg  |
| Customs tariff number | 94039910  |
| ETIM 9                | EC002621  |
| ECLASS 8.0            | 27189262  |
| Product description   | Castor module for VX IT, for W: 800 mm, for easy movement directly at the point of use, for mounting directly on the enclosure. |

## Tender text

Castor module for W: 800 mm

For easy movement on site, can be mounted directly on the IT rack.

Scope of delivery:

1 transport module with 2 castors

1 transport module with 2 baying clamps, fixed

Assembly parts