### Rittal - The System.

Faster - better - everywhere.





# VX 5302.166 Depth stays

State: 05.11.2025 (Source: rittal.com/ua-en)



# VX 5302.166 - Depth stays for 482.6 mm (19") mounting angles

L-shaped mounting angles, also for accommodating server system installation kits.

#### **Features**

Model No.	VX 5302.166
Design	for VX IT 482.6 mm (19") mounting angles, standard
	for VX IT 482.6 mm (19") mounting angles, dynamic
Product description	To accommodate 19" mounting angles.
Benefits	Particularly high load capacity up to 15,000 N
	Enhanced stability thanks to improved load distribution
	Symmetrical or asymmetrical installation supported
	More space for cable routing or integration of a Liquid Cooling Unit
	(LCU) with one-sided, asymmetrical (laterally offset) installation
	Ideal for integrating 482.6 mm (19") mounting angles for alternative
	installation with 21", 23", or 24" components
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 9005
Supply includes	Depth stays
	Assembly parts
Assembly instruction	For the attachment of mounting angles in enclosures that are
	greater than 1000 mm deep and greater than 600 mm wide, an
	additional support rail for VX IT is required
To fit	Enclosure type: VX IT, standard
	VX IT, dynamic
	Width: = 600 mm
	Depth: = 1,200 mm
Packs of	2 pc(s).
Net weight	3.5
Gross weight	3.652
——————————————————————————————————————	3.032

© Rittal 2025

#### **Features**

PCF per pack (cradle-to-gate)	27.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177955608
ETIM 9	EC002620
ECLASS 8.0	27189261

## **Approvals**

Explanations Manufacturer's declaration

© Rittal 2025 3