


Rittal – The System.

Faster – better – everywhere.



IT 5302.201

Vent trim panel, 482.6 mm (19")

State: 22.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 5302.201 - Vent trim panel, 482.6 mm (19")

For venting enclosures and housings.

Features

| | |
|-------------------------|--|
| Model No. | IT 5302.201 |
| Product description | For targeted air infeed from the front zone into the 482.6 mm (19") level. |
| Benefits | Vented surface area approx. 85 % perforated |
| Applications | Targeted routing of cold air from the raised floor via the front to the rear for cooling separate components |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Installation dimensions | Installation depth for components: 482.6 mm Installation width for components: 19" |
| Units | 1 U |
| Packs of | 1 pc(s). |
| Net weight | 0.234 kg |
| Gross weight | 0.237 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000331 |
| ECLASS 8.0 | 27189272 |
| Product description | Ventilation panel, 482.6 mm (19"), 1 U, sheet steel, RAL 9005 |