Rittal – The System.

Faster – better – everywhere.





CP 6320.400 Command panels with handle strips

State: 14.12.2025 (Source: rittal.com/ua-en)



CP 6320.400 - Command panels with handle strips

Operating housings with modern sheet steel handle strips, with support arm cut-out \emptyset 130 mm to fit support arm system CP 60 / 120 / 180, service access optionally from the front or rear, aluminium front panel easily removable for machining, protection category IP 55.



Features

Model No.	CP 6320.400
Material	Enclosure and door: Sheet steel
	Handle strips: Aluminium
	Front panel: Aluminium
	Cover caps: Plastic
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside,
	textured paint
	Handle strip: Natural anodised
	Front panel: Natural anodised
Colour	Enclosure and door: RAL 7035
	Handle strip: Natural anodised
	Front panel: Natural anodised
	Cover caps: similar to RAL 7024
Supply includes	Enclosure with cut-out and reinforcement for support arm
	connection Ø 130 mm
	Front with maximum cut-out, covered with easily machinable 3 mm
	aluminium front panel
	Side handle strips and cover caps
	Cam lock with 3 mm double-bit insert
	Integral interior installation bracket with TS system punchings

© Rittal 2025 2

Features

Dimensions	Width: 500 mm
	Height: 500 mm
	Depth: 210 mm
IP protection category to IEC 60 529	IP 55
Design	Servicing access from the rear
Note	The support arm connection and door hinge may be swapped over
	by rotating the enclosure
	Optional: Support arm connection Ø 130 mm, preformed off-centre
	in the reinforcement plate, easily drilled out
	Lock systems for servicing access from the rear: 27 mm lock
	inserts, type A, lock cylinder, plastic handles and T handles, type B
Basic material	Aluminium
Lock	Lock version: Cam
	Number of locks: 2
	Lock insert: 3 mm double-bit
Packs of	1 pc(s).
Net weight	13.537
Gross weight	14.249
EAN	4028177693999
ECLASS 8.0	27180505

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3