
## Rittal - The System.

Faster – better – everywhere.





SK 7109.035

# Digital enclosure internal temperature display and thermostat

State: 16.11.2025 (Source: rittal.com/ua-en)



# SK 7109.035 - Digital enclosure internal temperature display and thermostat integrated into a patch panel 1 U

#### **Features**

Model No.	SK 7109.035
Product description	Including cable attachment for connection cable and label holder.
Technical specifications	Three-digit, 7-segment display Option of switching between °C/°F Includes 1800 mm long NTC sensor Two relay outputs as change-over contact and normally open contact (max. contact load 230 V, 6 A) Freely selectable switching difference
Colour	RAL 7035
Packs of	1 pc(s).
Setting range	5 °C55 °C
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz 24 V - 60 V (DC)
Net weight	0.72
Gross weight	0.86
Customs tariff number	94039910
EAN	4028177165649
ETIM 9	EC004587
ETIM 8	EC004587
ECLASS 8.0	27210707

## **Approvals**

© Rittal 2025

#### **Approvals**

Certificates

**EAC** 

#### Tender text

Rittal patch panel with temperature display and thermostat, RAL 7035

Small dimensions

Depth: 100 mm

."The three-digit, 7-segment display is 13 mm high and easy to read

.,,can be switched between °C/°F

."The display can be used in temperatures ranging from

+5°C to +55°C

.,,With 1800 mm long NTC sensor

Rated operating voltage: 100 - 230 V, 50/60 Hz und 24 - 60 V (DC),

special voltages available on request.

."Two relay outputs used as change-over contacts (max. contact load 230V, 6A)

."Switching difference can be freely selected

."The freely adjustable setpoint values can be set via

the membrane keyboard mounted at the front.

Setting range: +5°C to +55°C

."Display and switching accuracy ± 2 K

.,,Mounting cutout 68 x 33 mm

."Minimum and maximum recorded temperatures are saved until the next reset.

Material: Spray finished in RAL 7035