

**Rittal – The System.**

Faster – better – everywhere.



**DK 7186.035**

# Component shelf for frame attachment

State: 11.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7186.035 - Component shelf for frame attachment for enclosure widths 600 mm, 800 mm

For installation in enclosures without 482.6 mm (19") accommodation.

## Features

|                      |   |
|----------------------|---|
| Model No.            | DK 7186.035   |
| Design               | Slotted   |
| Product description  | For frame attachment, for installation in enclosures without 482.6 mm (19") accommodation.  |
| Benefits             | Mounting bolts or mounting rails may be installed on a 25 mm pitch pattern in the enclosure depth.<br>Mounting hole for handles provided.   |
| Applications         | For installation in enclosures without 482.6 mm (19") accommodation   |
| Material             | Sheet steel   |
| Surface finish       | Spray-finished  |
| Colour               | RAL 7035  |
| Supply includes      | Component shelf, slotted<br>4 pc(s). fixing bolts   |
| Installation options | Static installation: Component shelf, 50 kg with fixing bolts on punched section without mounting flange<br>Static installation: Component shelf, 100 kg with mounting rails on punched sections without mounting flange<br>Depth variable: Component shelf, 50 kg with telescopic slides on punched sections without mounting flange |
| Load capacity        | 50 kg area load   |
| Assembly instruction | Additionally, two punched sections with mounting flanges are required for the inner mounting level  |
| Note                 | Max. depth of component shelves = Enclosure depth - 100 mm.   |

# Features

|                               |  |
|-------------------------------|--|
| Dimensions                    | Width: 671 mm<br>Height: 29 mm<br>Depth: 600 mm  |
| To fit                        | Enclosure type: VX<br>VX IT<br>TS IT<br>Width: 800 mm  |
| Packs of                      | 1 pc(s).   |
| Net weight                    | 4.795 kg   |
| Gross weight                  | 5.047 kg   |
| PCF per pack (cradle-to-gate) | 19.2 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 94039910   |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |
| Product description           | DK Component shelf, WHD: 671x29x600 mm, 50 kg, Slotted, For W: 800 mm, RAL 7035                                |

# Tender text

Component shelf for 800 mm wide network enclosures

Component shelf made from 1.5 mm sheet steel for use in 800 mm wide network enclosures. The component shelf has slots for preventing heat accumulation and can be loaded up to a maximum of 50 kg. The height of the fitted component shelves can be adjusted using the 25 mm pitch pattern in network enclosures with a DIN pitch pattern but is infinitely adjustable in network enclosures with aluminium frames.

Material: sheet steel

Surface finish: RAL 7035

Dimensions: W x D: 671 x 600 mm