

Rittal – The System.

Faster – better – everywhere.



AS 4050.456 Crimping machine RC

State: 04.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.456 - Crimping machine RC

Electropneumatic crimping machine with 5-way magazine for processing insulated wire end ferrules in various cross-sections on a reel.



Features

| | |
|---------------------------|---|
| Model No. | AS 4050.456 |
| Design | Touchscreen display Select the wire cross-section via touchscreen Support may be fitted with a maximum of 23,000 wire end ferrules |
| Product description | |
| Benefits | Easy to operate Secure, fast processing of insulated wire end ferrules No set-up time, thanks to automatic tool change Simple, quick component mounting No changing of the wire end ferrules required due to 5-way magazine |
| Technical specifications | Crimping range 0.5 - 2.5 mm ² (AWG 20 - 14) Crimping length 8 and 10 mm Insertion length 27 mm (1.06 in.) |
| Note | The standard crimping form is trapezoid – others available on request |
| Dimensions | Width: 335 mm Height: 565 mm Depth: 485 mm |
| Compressed air connection | 5.5 bar |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |

Features

| | |
|-----------------------|-----------------|
| Apparent power | 16 VA |
| Compression | Trapezoid crimp |
| Cycle time | 2 s |
| Packs of | 1 pc(s). |
| Net weight | 24.8 |
| Gross weight | 25.4 |
| Customs tariff number | 84624900 |
| EAN | 4028177930865 |
| ETIM 9 | EC002778 |
| ETIM 8 | EC002778 |
| ECLASS 8.0 | 17130101 |