

Rittal – The System.

Faster – better – everywhere.



AS 4055.481 Hole punch set, PG

State: 13.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.481 - Hole punch set, PG for sheet steel

For punching round cut-outs

Features

Model No.	AS 4055.481
Design	With 3 cutting points
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	5 female dies 5 male dies 2 tension screws with ball bearing Ø 9.5 x 50 mm HSS pilot drill Ø 11 mm 1 tube of lubricant paste Plastic case
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm
Ø punch	15.2 mm 18.6 mm 20.4 mm 22.5 mm 28.3 mm
Note	When operating with wrenches, tension screws with ball bearings should be used.
Suitable for hydraulic bolt order number	4055.661
Packs of	1 pc(s).
Net weight	0.909 kg
Gross weight	0.91 kg
Customs tariff number	82051000
ETIM 9	EC002121

Features

ETIM 8	EC002121
ECLASS 8.0	21049047
Product description	Sheet metal punches set, PG Ø 15,2/18,6/20,4/22,5/28,3
