


Rittal – The System.

Faster – better – everywhere.



SZ 4140.110 Compact light

State: 16.12.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4140.110 - Compact light

Compact light – slimline, space-saving light for use inside the enclosure



Features

Model No.	SZ 4140.110
Benefits	Slimmer: Around 50% less height and depth and therefore around 75% less volume than conventional lights Faster: Universal fast attachment to the TS slots via clips, screws, or powerful magnets (optional). Simply slide in at the side or rear, fit the light, and it's done! Door-operated switch can also be connected via a 2-pole connector Transparent light cover, grooved on the inside
Colour	Similar to RAL 7035
Supply includes	Compact light with clip and screw mounting kits Light Light cover Connection cable Assembly parts
Power consumption	8 W
Length of connection cable	3 m
Mounting distance screws	475 mm

Features

Ballast	Electronic ballast
Connection options	Integral connection cable with open end Door-operated switch
Light	Fluorescent lamp T5
Protection class	II (all-insulated)
Switch (type)	Integral on/off/door-operated switch
Cable deflection via rear possible	Yes
Light cover	Yes
Light – installation type	Screw-fastening Clip attachment Magnetic attachment (accessory)
Rated impulse withstand voltage, phase to earth	Depending on the power pack
Rated impulse withstand voltage, phase to phase	Depending on the power pack
Rated insulation voltage	Depending on the power pack
With DC	0.35 A
Mounting distance clip/magnet	400 mm
Installation options	TS horizontal section of the roof frame: direct TS, SE vertical section: direct SE extrusions at the front and rear of the roof frame: direct SE extrusions at the side of the roof frame: direct AE, CM, TP: with magnet mounting kit AE: with rail for interior installation
Note	Door-operated switch can also be connected via a 2-pole connector
Note on Model No.	Cable deflector across rear possible
Dimensions	Width: 455 mm Height: 59 mm Depth: 24 mm
Operating temperature range	-15 °C...45 °C
Storage temperature range	-20 °C...70 °C

Features

Rated operating voltage	24 V (DC)
IP protection category to IEC 60529	IP 20
Packs of	1 pc(s).
Net weight	0.48
Gross weight	0.486
Customs tariff number	94054990
EAN	4028177550292
E-Number Sweden	E4302502
ECLASS 8.0	27189241