


Rittal – The System.

Faster – better – everywhere.



VX 5301.518 Castor module

State: 25.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.518 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

Features

Model No.	VX 5301.518
Product description	For mobile use even with preconfigured enclosures. The castor module is screw-fastened to the structure directly underneath the base frame and is suitable for transporting configured enclosures on flat ground and inside buildings.
Supply includes	1 transport module with 2 castors 1 transport module with 2 castors, fixed Assembly parts
Dimensions	Width: 756 mm Height: 203 mm Depth: 79 mm
Assembly instruction	The base area must be open at the mounting points
To fit	Enclosure type: VX: = 800 mm Enclosure type: VX IT
Load capacity	Max. admissible load: Static 15,000 N Max. admissible load: Dynamic 10,000 N
Note	The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground.
Packs of	1 pc(s).
Net weight	11.5
Gross weight	12.12
Customs tariff number	94039910
EAN	4028177952515
E-Number Sweden	E7282571
ETIM 9	EC002621
ECLASS 8.0	27189262

Tender text

Castor module for W: 800 mm

For easy movement on site, can be mounted directly on the IT rack.

Scope of delivery:

1 transport module with 2 castors

1 transport module with 2 baying clamps, fixed

Assembly parts