


Rittal – The System.

Faster – better – everywhere.



DK 5302.015 Air baffle plate

State: 07.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.015 - Air baffle plate for VX IT 482.6 mm (19") mounting angles, standard

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



Features

Model No.	DK 5302.015
Benefits	To selectively boost the energy efficiency of your climate control system Vertical brush strip for collision-free shielding with installed rail systems on the outer mounting level.
Applications	To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.
Material	Sheet steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB
Surface finish	Spray-finished
Colour	RAL 9005
Supply includes	2 vertical trim panels 2 horizontal trim panels 4 brush strips 4 cellular PU foam pieces Assembly parts 6 blanking panels, 482.6 mm (19"), 1 U

Features

Assembly instruction	<p>The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning.</p> <p>The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles.</p> <p>482.6 mm (19") mounting cut-outs integrated within the partitioning areas may optionally be sealed with the supplied blanking panels, or used to install additional components or for cable routing. Please see the product-specific scope of supply.</p>
To fit	<p>Width: = 800 mm</p> <p>Height: = 2,200 mm</p>
Packs of	1 pc(s).
Net weight	8.7
Gross weight	9.2
PCF per pack (cradle-to-gate)	35.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177955301
E-Number Sweden	E7282587
ETIM 9	EC000331
ECLASS 8.0	27189272