

Rittal – The System.

Faster – better – everywhere.



IT 5302.026 Combination rails

State: 23.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 5302.026 - Combination rails for 482.6 mm (19")

Features

Model No.	IT 5302.026
Applications	For cable routing and strain relief on the 482.6 mm (19") level
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts for the combination rail, without assembly parts for fixing the cables
Installation options	Within the 482.6 mm (19") mounting level, on the 482.6 mm (19") system punchings
Dimensions	Height: 1 U
To fit	Enclosure type: TS IT VX IT TX CableNet
Packs of	4 pc(s).
Net weight	1.348 kg
Gross weight	1.4 kg
PCF per pack (cradle-to-gate)	5.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	83024200
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	Combination rail, 1 U, for 482.6 mm (19"), for cable routing and strain relief at the 19" level, for installation within the 19" mounting level or at the 19" system punchings