

**Rittal – The System.**

Faster – better – everywhere.



**IT 5302.201**

**Vent trim panel, 482.6 mm (19")**

State: 09.07.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 5302.201 - Vent trim panel, 482.6 mm (19")

For venting enclosures and housings.

## Features

|                         |  |
|-------------------------|--|
| Model No.               | IT 5302.201  |
| Product description     | For targeted air infeed from the front zone into the 482.6 mm (19") level.                                   |
| Benefits                | Vented surface area approx. 85 % perforated  |
| Applications            | Targeted routing of cold air from the raised floor via the front to the rear for cooling separate components |
| Material                | Sheet steel  |
| Surface finish          | Spray-finished   |
| Colour                  | RAL 9005   |
| Installation dimensions | Installation depth for components: 482.6 mm<br>Installation width for components: 19"                        |
| Units                   | 1 U  |
| Packs of                | 1 pc(s).   |
| Net weight              | 0.234 kg   |
| Gross weight            | 0.237 kg   |
| Customs tariff number   | 94039910   |
| ETIM 9                  | EC000331   |
| ECLASS 8.0              | 27189272   |
| Product description     | Ventilation panel, 482.6 mm (19"), 1 U, sheet steel, RAL 9005  |