# Rittal – The System.

Faster - better - everywhere.





# DK 7979.142 PDU basic


State: 29.10.2025 (Source: rittal.com/ua-en)



## DK 7979.142 - PDU basic

High-end IT rack power distribution: Robust PDU with compact basic power distribution for the IT environment.







## **Features**

Model No.	DK 7979.142	
Product description	Compact basic power distribution. Thanks to the PDU basic, any IT rack can easily be equipped with a professional power distribution system. Depending on the PDU design, horizontal mounting in the 482.6 mm (19") level or vertical mounting (including in the zero-U space) is possible.	
Benefits	For vertical mounting, it may be attached in the zero-U space of the Rittal VX IT or TS IT rack with no need for tools Colour coding of phases and fuse circuits (L1=pink, L2=black, L3=white) Tool-free divider kit for VX IT	
Material	Extruded aluminium section, anodised Slots: Plastic	
Supply includes	Connector lock for IEC C14 and C20 connectors Assembly parts	
Options	Type 3 overvoltage protection with interchangeable arresters while operational, with status monitoring, suitable for integration into PDU enclosure Other enclosure colours are available	

© Rittal 2025

# Features

Dimensions	Width: 44 mm Depth: 70 mm Length: 1,495 mm	
No. of sockets and type	42 x C13	
Rated operating voltage	400 V (AC)	
Rated current (max.)	16 A	
Power consumption	11 kW	
Infeeds	Qty.: 1 Phases per infeed: 3~	
Length of connection cable	3 m	
Type of electrical connection	CEE	
Directives	EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU	
Standards	EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21	
Operating temperature range	5 °C50 °C	
Ambient humidity (non-condensing)	1095 %	
Storage temperature range	-20 °C70 °C	
To fit	Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm	
Packs of	1 pc(s).	
Net weight	4.3	
Gross weight	4.6	
Customs tariff number	85366990	
EAN	4028177947580	
	E8407024	

© Rittal 2025 3

#### **Features**

ETIM 9	EC002762	
ETIM 8	EC002762	
ECLASS 8.0	27142604	

### **Approvals**

**Explanations** 

Declaration of conformity

#### Tender text

Rittal PDU basic Model No.: DK 7979.142

Compact power distributor for deployment in IT server and network enclosures. Vertical installation in the Zero-U space using the supplied universal brackets for common IT racks. Suitable for tool-free quick assembly in the Rittal VX IT and TS IT racks using the special supplied plug-%-play fastener. Robust aluminium housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19 as well as CEE 7/3 (earthing-pin) and BS 1363 (UK), depending on the type (see below for details). The IEC C13 / C19 output slots can be protected with a lock against unintentional removal of the connectors. Unused slots can be closed wicht slot covers available as accessories. This precludes an unintentional overloading of individual phases an circuits. The fuse circuits and phases are colour-coded for multiphase PDU variants. A fixed-mounted connection cable with IEC C20 or CEE connector appropriate for the variant makes the PDU available for immediate deployment. Optinally, an overvoltage protection module (type3) can be placed on the PDU at the infeed; the overvoltage

© Rittal 2025

protection module is equipped with arrestors that can be replaced during operation. For intelligent PDUs, the status is monitored via the network interface, the PDU basic has a floating alarm contact for monitoring the overvoltage protection.

The warranty for proper operation is 24 months.

Technical specifications basic

Input voltage range (L1-L2-L3/N/PE): 400 VAC, 50-60Hz

input current: 16A No. of phases: 3

Marking of phases (3-phase PDU only L1, L2, L3):

Rittal Power Pink, black, white

Number of slots type IEC 60320/C13 (total): 42

Number of slots type IEC 60320/C13

(per phase/fuse): 14

Number of slots type IEC 60320/C19 (total): -

Number of slots type IEC 60320/C19

(per phase/fuse): -

Number of slots type CEE 7/3 (total): -

Number of slots type CEE 7/3 (per phase/fuse): -

No. of circuit brakers: -

Hydraulic-magnetic protective circuit-breaker: 16 A

Connector PDU input:

EN 60309 / CEE (3L+N+PE, 6h) Length of connection cable: 3m Connection cable type: H05-VV

No. of wires: 5

Cable cross-section: 2,5 mm<sup>2</sup> PDU housing width: 44mm PDU housing depth: 70mm PDU housing height: 1495mm

PDU material: Aluminium, anodised, in RAL 9005 (black),

other colours available on request

PDU mounting adaptor (VX IT / TS IT)-Mounting options:

Frame+Zero-Uspace+cable route, fuse monitoring

Conformity: CE Standards:

Safety: EN 62368

EMC: EN 55022 / B

EN 61000-4-2

EN 61000-4-3

EN 61000-6-2

© Rittal 2025 5

EN 61000-6-3

Low Voltage Directive: 2014/35/EU

EMC Directive: 2014/30/EU MTBF (at 40°C) 100.000 hours

Protection category: IP20 (EN 60529)

Protection class: Class 1

Pollution degree: 2

Overvoltage category: II

Environmental properties: 2011/65/EU (RoHS 2), WEEE

Storage temperature: -20 °C to +70 °C Ambient temperature: +5°C to +50°C

Ambient humidity 10 - 95% rel. humidity, non-condensing Operating altitude (max. above mean sea level): 3000 m

Connector lock for C14 and C20 connectors:

1x (further connector locks optional - DK 7979.020)

Covers C13 (optional accessory): DK 7955.010 Covers C19 (optional accessory): DK 7955.015

Warranty: 24 months

Type: Rittal PDU basic, Model No.: DK 7979.142

PDU Basic 16A/3P CEE 42xC13

© Rittal 2025 6