Rittal - The System.

Faster – better – everywhere.





DK 7979.204 PDU metered

State: 26.11.2025 (Source: rittal.com/ua-en)



DK 7979.204 - PDU metered

High-end IT rack power distribution: Smart PDU with energy measurement per phase, i.e. output requirement of an entire IT rack







Features

| Model No. | DK 7979.204 |
|---------------------|--|
| Design | 482.6 mm (19") version |
| Product description | High-end power distribution in a compact design for IT network and server racks. With power measurement at the infeed or per phase. |
| Benefits | For vertical mounting, it may be attached in the zero-U space of the Rittal VX IT or TS IT rack with no need for tools Colour coding of phases and fuse circuits (L1=pink, L2=black, L3=white) Tool-free divider kit for VX IT PDU self-supplied, no external power supply required Measurement accuracy ± 1% (kWh) to EN 62 053-21 Integral real-time clock with battery buffering (max. 10 years, battery replaceable) Integral electromagnetic buzzer for acoustic alarms Adjustable limit values (warning/alarm) for voltage, current, output Operating hours meter, total and cyclical, resettable Power-saving design, minimal intrinsic power consumption |

Features

| Technical specifications | Display/controller unit in the PDU enclosure rotatable through 180° and replaceable Compact circuit-breaker (16 A - Carling type) Integral, fully-redundant power pack, power supply from all phases Error-tolerant PDU power supply redundant across all phases Voltage V, current A, frequency Hz Active power, active energy, apparent power, apparent energy Power factor (cosPhi) and phase angle Zero conductor current measurement/load imbalance detection Fuse monitoring for PDUs with integral fuse Bright TFT display, 128 x 128 pixels (RGB) with back-lighting and energy-saving mode to display output data and basic PDU configuration Position sensors for display rotation and correct PDU representation on the website Power LED to indicate voltage |
|--|--|
| Material | Aluminium section, black anodised Slots: Plastic |
| Supply includes | Assembly parts |
| Options | CMC III CAN bus sensors may be connected for ambient monitoring, max. 16 sensors |
| Measurement functions, description | Measurement per phase or infeed Powerful CPU (ARM Cortex A8) Digital input (floating contact) Additional alarm output/relay output (changeover contact) |
| | Additional alarm output/relay output (changeover contact) |
| Dimensions | Height: 44 mm Depth: 144 mm Length: 450 mm |
| Dimensions No. of sockets and type | Height: 44 mm Depth: 144 mm |
| | Height: 44 mm Depth: 144 mm Length: 450 mm |
| No. of sockets and type | Height: 44 mm Depth: 144 mm Length: 450 mm 4 x C13 / 2 x C19 |
| No. of sockets and type Rated operating voltage | Height: 44 mm Depth: 144 mm Length: 450 mm 4 x C13 / 2 x C19 230 V (AC) |
| No. of sockets and type Rated operating voltage Rated current (max.) | Height: 44 mm Depth: 144 mm Length: 450 mm 4 x C13 / 2 x C19 230 V (AC) 32 A |

© Rittal 2025

3

Features

| Type of electrical connection | CEE |
|---|--|
| Interfaces | USB 2.0 port (USB-A) for mass configuration, firmware updates & data logging CAN bus interface (RJ 45) for a maximum of 16 ambient sensors Serial interface RS232 (RJ12) for LTE unit, scripting, CLI Use of own certificates/TLS 1.2 E-mail forwarding in case of alarm (SMTP) User administration including rights management LDAP(S)/Radius/Active Directory connection Syslog server connection (max. 2 servers) Fully redundant Ethernet interface 10/100/1000 Mbit/s |
| Number RJ45 ports for sensor units max | 2 |
| Directives | EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU |
| Standards | EN 62368-1 EN 61000-3 EN 61000-4 EN 62053-21 |
| Protocols | Web server (HTTP, HTTPS, SSL) SSH, Telnet, NTP TCP/IP v4 & v6, DHCP, DNS SNMP v1, v2c & v3, Modbus/TCP, OPC-UA MIB for linking into 3rd party DCIM software FTP/SFTP (update/file transfer) |
| Operating temperature range | 5 °C50 °C |
| Ambient humidity (non-condensing) | 1095 % |
| Storage temperature range | -20 °C70 °C |
| To fit | Enclosure type: VX IT enclosure frame: ≥ 800 mm Enclosure type: VX IT 19" mounting angles: ≥ 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 3.38 |
| Gross weight | 3.68 |

Features

| Customs tariff number | 85369095 |
|-----------------------|---------------|
| EAN | 4028177947627 |
| E-Number Sweden | E8407028 |
| ETIM 9 | EC002762 |
| ETIM 8 | EC002762 |
| ECLASS 8.0 | 27142604 |

Approvals

| Approvals | TÜV |
|--------------|---------------------------|
| Explanations | Declaration of conformity |

Tender text

Compact power distributor for deployment in IT server and network enclosures. Robust aluminium housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19 as well as CEE 7/3 (earthing-pin) and BS 1363 (UK), depending on the type (see below for details). The IEC C13 / C19 output slots can be protected with a lock against unintentional removal of the connectors. Unused slots can be closed with slot covers available as accessories. This precludes an unintentional overloading of individual phases an circuits. The fuse circuits and phases are colour-coded for multiphase PDU variants. A connection cable with IEC C20 or CEE connector appropriate for the variant makes the PDU available for immediate deployment.

The PDU metered has extensive measurement functions for the current and power monitoring of each phase. The integral TFT colour display anables the basic configuration setting and quick access of the electrical consumption data. Two Gigabit network interfaces and the integrated Web server allow access and data transmission using various protocols. The consumption parameters can be forwarded to a DCIM software via SNMP, OPC-UA, Modbus/TCP. For monitoring the ambient parameters, up to 16 sensors (for example temperature / humidity / smoke / leakage / access) as well as VX IT and TS IT handle systems from the CMC accessories program can be connected to the CAN sensor interface.

The warranty for proper operation is 24 months.

Technical specifications metered

Input voltage range (L/N/PE): 230 VAC, 50-60Hz

input current: 32A

No. of phases: 1

Marking of phases (3-phase PDU only L1, L2, L3):

Rittal Power Pink, black, white

Number of slots type IEC 60320/C13 (total): 4

Number of slots type IEC 60320/C13

(per phase/fuse): 4 / 2

Number of slots type IEC 60320/C19 (total): 2

Number of slots type IEC 60320/C19

(per phase/fuse): 2 /1

Number of slots type CEE 7/3 (total): -

Number of slots type CEE 7/3

(per phase/fuse): -

No. of circuit brakers: 2

Hydraulic-magnetic protective circuit-breaker: 16 A

Connector PDU input:

EN 60309 / CEE (L+N+PE, 6h) Length of connection cable: 3m Connection cable type: H05-VV

No. of wires: 3

Cable cross-section: 4 mm² PDU housing width: 450mm PDU housing depth: 144mm

PDU housing height: 44mm (1HU)

PDU material: Aluminium, anodised, in RAL 9005 (black)<(>,<)>

other colours available on request

PDU mounting adaptor (VX IT / TS IT) – Mounting options:

Frame + Zero-U space + cable route

Measurement functions: Measurement per phase or infeed

Values recorded (per phase):

Voltage (V), current (A), frequency (Hz), Power factor<(>,<)>

Active power (kW), active energy (kWh)<(>,<)>

apparent power (kVA)

Active power(kW),neutral conductor current measurement<(>,<)>

fuse monitoring (at 32 A)

Optional: Residual current monitoring (RCM)

AC + DC (RCM Typ B)

max. 6 measurement points per PDU possible

(input / per phase / per fuse)

0 mA - 100 mA je RCM

Voltage measuring range: 90V - 255V

Voltage resolution 0.1V

Current measuring range 0 - 16A/32A

Current resolution 0.1A

Measuring accuracy typ. ± 1% according to IEC/EN 62 053-21

Freely adjustable limit values (warning/alarm) for

for voltage, current, power: Yes Operating hours counter: Yes Controllerboard: can be rotated

and replaced during operation

Display: TFT, RGB 128x128 pixels

Network interface: 2x RJ45, per 10/100/1000 MBit/s

Supported protocols:

IPv4 / IPv6, integral web server

HTTP, HTTPS, SSL, SSH, NTP, Telnet

TCP/IP v4 and v6, DHCP, DNS, NTP, Syslog

SNMP v1, v2c und v3, Traps<(>,<)>

FTP/SFTP (update/file transfer)

OPC-UA, Modbus/TCP<(>,<)>

FTP/SFTP (update/file transfer)<(>,<)>

E-mail forwarding (SMTP)

User administration including rights management: Yes

LDAP(S)/Radius/Active Directory connection: Yes

USB port for firmware update+data logging functions: Yes

CAN bus interface: RJ45, for connecting 16 sensors

CAN sensor types: Temperature<(>,<)>

temperature/humidity (combined),infrared access sensor<(>,<)>

leakage, NH measurement module, smoke alarm, vandalism<(>,<)>

airflow, EFD, differential pressure<(>,<)>

VX IT / TS IT handle system

Plug & play drivers-Rittal RiZone DCIM software: Yes

Digital input: 1

Alarm relay: 48 V DC/2 A

Acoustic signal encoder

Serial interface

Conformity: CE

Standards:

Safety: EN 62368

EMV:

EN 55022 / B

EN 61000-4-2

EN 61000-4-3

EN 61000-6-2

EN 61000-6-3

Safety Directive: 2014/35/EU EMC Directive: 2014/30/EU MTBF (at 40°C) 100.000 hours

Protection category: IP 20 (EN 60529)

Protection class: Class 1

Pollution degree: 2

Overvoltage category: II

© Rittal 2025

Environmental properties: 2011/65/EU (RoHS 2), WEEE

Storage temperature: -20 °C to +70 °C Ambient temperature: +5°C to +50°C

Ambient humidity 10 - 95% rel. humidity, non-condensing Operating altitude (max. above mean sea level): 3000 m

Connector lock for C14 and C20 connectors:

1x (further connector locks optional - DK 7979.020)

Covers C13 (optional accessory): DK 7955.010 Covers C19 (optional accessory): DK 7955.015

Warranty: 24 months

Type: Rittal PDU metered, Model No.: DK 7979.204

© Rittal 2025