

Rittal – The System.

Faster – better – everywhere.



SK 7980.000 Fan expansion kit

State: 06.07.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 7980.000 - Fan expansion kit

For retrofitting various fan units or to supplement the fan mounting plate

Features

| | |
|---|---|
| Model No. | SK 7980.000 |
| Product description | For use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate. |
| Supply includes | Fan Connection cable (0.61 m) Assembly parts |
| Air throughput, unimpeded airflow (with chopped-fibre filter) | At 50 Hz: 160 m ³ /h At 60 Hz: 180 m ³ /h |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Power consumption Pel | At 50 Hz: 15 W At 60 Hz: 14 W |
| Dimensions | Width: 119 mm Height: 119 mm Depth: 38 mm |
| Operating temperature range | -10 °C...55 °C |
| Noise level | At 50 Hz: 37 dB(A) At 60 Hz: 37 dB(A) |
| Packs of | 1 pc(s). |
| Net weight | 0.6 kg |
| Gross weight | 0.671 kg |
| Customs tariff number | 84145915 |
| ETIM 9 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | DK Fan expansion kit, for use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate, WxHxD: 119x119x38 mm, 230 V, 1 ~, 50/60 Hz |

Tender text

Fan expansion kit for fan mounting plate

Rated operating voltage: 230V; Power consumption: 19/18

W at 50/60 Hz;

Air throughput (unimpeded air flow): 160 - 180 m³/h at
50/60 Hz;

Temperature range: -10°C to +55°C

Dimensions (W x H x D): 119 mm x 119 mm x 38 mm