
Rittal - The System.

Faster – better – everywhere.





VX 8640.009

Base/plinth corner piece with base/ plinth trim panels, front and rear, 100 mm

State: 09.11.2025 (Source: rittal.com/ua-en)

NCLOSURES

OWER DISTRIBUTION

LIMATE CONTROL

T INFRASTRUCTURI

SOFTWARE & SERVICES

VX 8640.009 - Base/plinth corner piece with base/plinth trim panels, front and rear, 100 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Heavy-duty base/plinth corner pieces with moulded self-positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover.

Features

Model No.	VX 8640.009
Product description	High-load capacity base/plinth corner pieces with moulded self- positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/ plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover.
Material	Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic
Colour	RAL 9005
Supply includes	4 base/plinth corner pieces, 100 mm high 4 corner covers 1 baying cover 2 base/plinth trim panels, front/rear, 100 mm high Assembly parts
Note	Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth
Dimensions	Height: 100 mm

© Rittal 2025 2

Features

To fit	Enclosure type: VX VX IT VX SE TS IT TX CableNet Width: = 1,800 mm
Type rating to UL 50E	Type 1 Type 12
Weight/pack	9.03 kg
Packs of	2 pc(s).
Net weight	8.9
Gross weight	9.04
Customs tariff number	94039910
EAN	4028177958821
E-Number Sweden	E3465368
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals UL + C-UL - FTTA