Rittal - The System.

Faster – better – everywhere.





VX 8660.022

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 25.11.2025 (Source: rittal.com/ua-en)

NCLOSURES

OWER DISTRIBUTION

LIMATE CONTROL

T INFRASTRUCTURI

SOFTWARE & SERVICE

VX 8660.022 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, sheet steel

Base/plinth corner pieces with trim panels for flexible cable entry.



Features

Model No.	VX 8660.022
Benefits	Reliable – Excellent stability of the base/plinth
	Flexible – Countless interior installation options with VX
	accessories
	Simple – Flush termination between the baying points
Material	Base/plinth corner piece: Sheet steel
	Base/plinth trim panel front/rear: Sheet steel
	Corner and baying cover: Plastic
Colour	RAL 9005
Supply includes	4 corner covers
	Assembly parts
	4 base/plinth corner pieces, 200 mm high
	1 base/plinth trim panel, front/rear, 200 mm high
	2 base/plinth trim panels, front/rear, 100 mm high
Note	Side base/plinth trim panels finish off a base/plinth unit or provide
	additional stabilisation between base/plinths or enable interior
	configuration of the base/plinth

© Rittal 2025

Features

Dimensions	Height: 200 mm
To fit	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW
	CX
	Width: = 600 mm
Type rating to UL 50E	Type 1
	Type 12
Weight/pack	7.27 kg
Packs of	2 pc(s).
Net weight	7.04
Gross weight	7.275
PCF per pack (cradle-to-gate)	27.7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177978133
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration