

# Rittal – The System.

Faster – better – everywhere.



## DK 7320.721 Handles, electromagnetic

State: 14.09.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7320.721 - Handles, electromagnetic for CMC III and IoT Interface

Handles may be integrated into various enclosure systems.

## Features

Model No.	DK 7320.721
Design	Comfort handle:with master key function
Product description	For control and monitoring via a central CMC III type control unit and IoT interface.
Colour	RAL 7035
Supply includes	2 adaptors for glazed door Cable clamps Adaptor for profile half-cylinders Connection cable (3 m) with RJ 12 connector Assembly parts
Lock type	Master key function (with emergency open function)
Rated current max.	0.1 A
No. of participants per IoT interface (max.)	16
No. of participating PU compact (max.)	2
No. of participating PU (max.)	16
Number subscribers per PDU note	Max. 5 p. for power supply with PoE
Packs of	1 pc(s).
Net weight	0.99
Gross weight	0.992
Customs tariff number	83024110
EAN	4028177390386
ETIM 9	EC000327

# Features

ECLASS 8.0

27409217

# Approvals

Explanations	Manufacturer's declaration
	Declaration of conformity

# Tender text

Comfort handle for TS 8 with master-key function,,,,,,,,,,  
The TS 8 handle includes the master key function.  
This means that, independently of the control system,  
the handle can always be opened using the master-key.  
The door can be released via the CMC-TC system.  
In addition an access unit (V1.1) and an access sensor  
(7320.530) should be used so that the door status can  
be polled.

Technical specifications:

- Rated voltage: 24 V DC
- Rated current: max. 100 mA
- Connection cable: Length 3 m, RJ 12 connector
- Connection cable: Length 2 m, RJ 12/RJ 12 connector
- Extension coupling: RJ 12/RJ 12 jack
- Temperature application range: +5°C to +40°C
- Protection category: IP 40