

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.050 Busbar support

State: 22.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.050 - Busbar support for flat copper busbars

For flat copper bars up to 800 A.

## Features

|                              |   |
|------------------------------|---|
| Model No.                    | SV 9340.050   |
| Design                       | UL-certified  |
| Material                     | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Colour                       | RAL 7035  |
| Rated operating voltage      | 1000 V, 3~<br>1500 V (DC)   |
| Electrical ratings UL (SCCR) | 14 kA - 600 V, support spacing 500 mm, 12 x 5/10 mm busbars<br>22 kA - 600 V, support spacing 500 mm, 15 x 5 - 25 x 10 mm busbars<br>25 kA - 600 V, support spacing 250 mm, 12 x 5/10 mm busbars<br>25 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars<br>30 kA - 600 V, support spacing 250 mm, 15 x 5 - 25 x 10 mm busbars<br>50 kA - 600 V, support spacing 350 mm, 30 x 5/10 mm busbars, Fuse Class L max. 800 A, JDDZ/7<br>54 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars, circuit breaker max. 600 A, DIVQ/7<br>65 kA - 480 V, support spacing 250 mm, 30 x 5/10 mm busbars, circuit breaker max. 600 A, DIVQ/7<br>73 kA - 600 V, support spacing 250 mm, 30 x 5/10 mm busbars, Fuse Class L max. 800 A, JDDZ/7 |
| Note on Model No.            | The use of a base tray is required for UL applications  |
| Number of poles              | 3-pole  |

# Features

---

|                                     |  |
|-------------------------------------|--|
| To fit Model No.                    | 3580000<br>3581000<br>3582000<br>3583000<br>3584000<br>3580100<br>3581100<br>3585005<br>3586005      |
| Internal attachment                 | Yes  |
| Centre-to-centre spacing of busbars | 60 mm  |
| To fit busbars                      | 12 x 5 - 30 x 10   |
| Packs of                            | 4 pc(s).   |
| Net weight                          | 0.668 kg   |
| Gross weight                        | 0.72 kg  |
| Customs tariff number               | 85469010   |
| ETIM 9                              | EC001166   |
| ECLASS 8.0                          | 27400607   |
| Product description                 | SV Busbar support, 3-pole, 60 mm centre-to-centre spacing, for busbar WxH: 12x5-30x10 mm, UL version |

---

# Approvals

---

|           |   |
|-----------|---|
| Approvals | ABS<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
|-----------|---|

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|

# Tender text

UL busbar support

UL busbar support with internal attachment, 3-pole

Technical specifications

Bar centre distance: 60 mm

Busbars E-Cu, 15 x 5 to 30 x 10 mm

Construction width: 20 mm

Length: 190 mm

Note

The use of a base tray is compulsory for  
UL applications.

System:

Rittal RiLine60