

Rittal – The System.

Faster – better – everywhere.



SV 9340.950

Bus-mounting fuse base D-Switch

State: 23.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.950 - Bus-mounting fuse base D-Switch

With integral visual fuse monitoring via flashing indicator and operating status display.

Features

| | |
|---|---|
| Model No. | SV 9340.950 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | Chassis: RAL 7035 Fuse holder: RAL 7001 |
| Supply includes | Retaining springs for D 01 and 10 x 38 mm fuses |
| Note | Wire end ferrules should be used with fine wire conductors |
| For bar systems with centre-to-centre spacing | 60 mm |
| Type of electrical connection | Box terminal |
| Fuse inserts | D 01 (with reducer) D 02 (with Neozed adaptor sleeve) 10 x 38 (with retaining spring) |
| Fuse inserts footnote | When using D 01 and 10 x 38 mm fuses, reducers must be used. Use of D 01 fuses optionally possible with adaptor sleeve for D 02 base/plinths. |
| Rated operating current max. | 63 A |
| Rated operating voltage | 400 V |
| Note | For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3) With integral visual fuse monitoring via flashing indicator and operating status display as well as cable routing for conductors up to 6 mm ² |
| Test specification | IEC/DIN EN 60 947-3 |
| Dimensions | Width: 27 mm Height: 226 mm |
| Connection of round conductors | 1.5 - 25 mm ² |

Features

| | |
|------------------------------------|---|
| To fit busbars | Height: 5, 10 mm |
| Voltage range for indicator lights | 100 - 400 V |
| Number of poles | 3-pole |
| Round conductor cross-section | 1.5 - 25 mm ² |
| Packs of | 3 pc(s). |
| Net weight | 0.975 kg |
| Gross weight | 1.04 kg |
| Copper weight (kg per piece) | 0.066 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001046 |
| ECLASS 8.0 | 27371402 |
| Product description | SV Bus-mounting fuse base, D-Switch, 63 A, 400 V, 3-pole, round conductor connection 1,5-25 mm ² |

Approvals

Explanations

Declaration of conformity