

SV 9343.010 - NH fuse-switch disconnecter

Features

| | |
|---|---|
| Model No. | SV 9343.010 |
| Material | Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Colour | Chassis: RAL 7035 Cover: RAL 7035/7001 |
| Clamping area for laminated copper bars | Clamping area width: 20 mm Clamping area height: 5 mm |
| For bar systems with centre-to-centre spacing | 60 mm |
| Cable outlet | Top/bottom |
| Type of electrical connection | Screw M8 |
| Rated operating current max. | 160 A |
| Rated operating voltage | 690 V, 3~ |
| For NH size | 00 |
| Note | The technical data may vary for UR applications. Applications to UR only in conjunction with "Special Purpose Fuses". |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts) |
| Dimensions | Width: 106 mm Height: 194 mm |
| Connection of round conductors | 10 - 95 mm ² |
| To fit busbars | Height: 5, 10 mm |
| Number of poles | 3-pole |
| Round conductor cross-section | 10 - 95 mm ² |
| Packs of | 1 pc(s). |

Features

| | |
|------------------------------|---------------|
| Net weight | 0.84 |
| Gross weight | 0.94 |
| Copper weight (kg per piece) | 0.2 |
| Customs tariff number | 85369095 |
| EAN | 4028177540262 |
| ETIM 9 | EC000249 |
| ECLASS 8.0 | 27371401 |

Approvals

| | |
|--------------|---|
| Approvals | C-UR CQC-CCC UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |