

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.635

## RiLineX CB component adaptor

State: 10.03.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.635 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 145 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | RX 9360.635   |
| Design                               | universal   |
| Benefits                             | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Material                             | Polyamide (PA 6)<br>Fire protection corresponding to UL 94  |
| Colour                               | RAL 9005<br>RAL 35745   |
| Supply includes                      | Including 3 connection space covers, 2 cross members and assembly parts   |
| IP protection category to IEC 60529  | IP 2XB  |
| Rated impulse withstand voltage Uimp | 12 kV   |

# Features

|                                   |   |
|-----------------------------------|---|
| Rated voltage                     | 690 V AC<br>690 V DC<br>600 V AC (UL)   |
| Rated insulation voltage Ui       | 1,000 V   |
| Overvoltage category              | 4   |
| Contamination level               | 3   |
| Number of poles                   | 3-pole  |
| Cable outlet                      | Top/bottom  |
| Cross-section                     | 29 mm <sup>2</sup><br>10 mm <sup>2</sup>  |
| To fit manufacturer (model)       | Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor. |
| To fit busbar system              | RiLineX<br>RiLine60   |
| Fundamental frequency             | 50...60 Hz  |
| Ambient humidity (non-condensing) | 10...90 %   |
| To fit busbars                    | 15 x 5/10<br>20 x 5/10<br>30 x 5/10   |
| Operating temperature range       | -25 °C...55 °C  |
| Storage temperature range         | -25 °C...75 °C  |
| Dimensions                        | Width: 145 mm<br>Height: 325.8 mm<br>Depth: 76.4 mm   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 4.52 kg   |
| Gross weight                      | 4.722 kg  |
| Copper weight (kg per piece)      | 2.64  |
| Customs tariff number             | 85369095  |

# Features

---

|                     |   |
|---------------------|---|
| ETIM 9              | EC001531  |
| Product description | RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 140 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. The cable outlet is easily converted to the top or bottom to suit individual requirements. |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |

---

# Tender text

RiLineX CB component adaptor (Universal Fix)

RiLineX CB component adaptor  
for 60 mm busbar systems.

Fastening is carried out using u-nuts in  
the two adjustable support rails.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 630 A

Connection: 290 mm<sup>2</sup>

Cable outlet: top/bottom

Dimensions: 145 mm x 325 mm x 76 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360635