Rittal - The System.

Faster – better – everywhere.





RX 9362.000 RiLineX NH fuse-switch disconnector

State: 03.11.2025 (Source: rittal.com/ua-en)



RX 9362.000 - RiLineX NH fuse-switch disconnector

RiLineX NH fuse-switch disconnector in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M8 screw terminal connection. Cable outlet can be at the top or bottom, as required.



Features

000	Model No.
n be locked and prepared for a lead seal	Benefits
est through separate opening	
mounting up to 250 A and simple adjustment to bu	
s 5/10 mm	
changeover of the cable outlet	
tion for simpler maintenance work	
ts also available with electronic fuse monitoring	
Polyamide (PA 6)	Material
ection corresponding to UL 94	
Contact tracks: Electrolytic copper, silver-plated	
RAL 9005 RAL 35745	Colour
	For bar systems with centre-to-
	centre spacing
om	Cable outlet
3	Type of electrical connection
	Rated operating current max.
	Rated operating voltage
om 3	For bar systems with centre-to- centre spacing Cable outlet Type of electrical connection Rated operating current max.

© Rittal 2025 2

Features

For NH size	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 195 mm Depth: 105 mm
Operating temperature range	-5 °C35 °C
Storage temperature range	-25 °C70 °C
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
To fit busbar system	RiLine60 RiLineX
Number of poles	3-pole
Utilisation category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) DC-22B (250 V/100 A)
Contamination level	3
IP protection category to IEC 60 529	IP 2XB
Fire load	14.2 MJ/m²
Power dissipation (max.)	19 W
Packs of	1 pc(s).
Net weight	1.015
Gross weight	1.023
Copper weight (kg per piece)	0.363
Customs tariff number	85369095
ETIM 9	EC001040
ETIM 9	EC001040

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity

© Rittal 2025