## Rittal – The System.

Faster - better - everywhere.





# SK 7990.000 Fan expansion kit

State: 07.12.2025 (Source: rittal.com/ua-en)



## SK 7990.000 - Fan expansion kit for VX IT, TS IT

Fan expansion kit with integral speed control for retrofitting to fan modules 5503.010, 5503.020 and 5503.025.

### **Features**

Model No.	SK 7990.000
Design	Without roof plate
Product description	Fan expansion kit with integral speed control for installing in fan modules 5503.xxx.
Benefits	Complete, ready-to-connect solution  Energy-efficient speed control with preset characteristic curve International approvals and multi-voltage capability for worldwide use
Material	Plastic
Colour	RAL 9005
Supply includes	Fan Protective grille Assembly parts Installation and Short User's Guide
Air throughput (at operating point)	150 m³/h
Rated operating voltage	24 V (DC)
Rated current max.	At 50 Hz: 0.32 A At 60 Hz: 0.32 A
Dimensions	Width: 119 mm Height: 25 mm Depth: 119 mm
IP protection category to IEC 60 529	IP 20
Speed	100 %
Note	Reduction in the specified air throughput to 150 m³/h at 25 Pa counterpressure

© Rittal 2025

### **Features**

Noise level (at operating point)	44 dB(A)
Operating temperature range	5 °C55 °C
Power consumption	7.7 W
Packs of	1 pc(s).
Net weight	0.3
Gross weight	0.308
Customs tariff number	84145915
EAN	4028177966345
ETIM 9	EC000320
ECLASS 8.0	27180716

© Rittal 2025 3

#### Tender text

SK fan expansion kit

Order No. SK 7990.000

Fan expansion kit for fan modules

with integrated speed controller for installation and expansion of fan

modules

e.g. manufacturer Rittal: SK 5503.XXX

incl. mounting material, fan grid and mounting instructions

Techn. data:

Rated operating voltage: 24 V DC

rated power: 7,7 W Rated current: 0.32 A

Air performance at operating point:

150 m³/h @ 25 Pa,

Air flow rate free-blowing: 192 m³/h

Sound pressure level free blowing: 46 dB (A)

Operating temperature range:

+5°C to + 55°C

Dimensions WxHxD: 119x25x119 mm

Protection class according to IEC 60529: IP 20

Material: plastic Color: RAL 9005

Order No. SK 7990.000 Manufacturer: Rittal

© Rittal 2025 4