

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.232 Current measurement module

State: 10.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.232 - Current measurement module

To extend the modular network analyser REM 801 with 8 additional current measurement channels.

## Features

Model No.	SV 9393.232
Design	REM 800-CT-8-LP null
Product description	To extend the modular network analyser REM 801 to a maximum of 92 current measuring channels or for connecting remote system parts etc. Up to 10 extension modules, such as current measurement modules with a maximum bus length of 100 m, may be connected via the internal bus or the bus connection modules.
Operating temperature range	-10 °C...55 °C
Storage temperature range	-25 °C...70 °C
Ambient humidity (non-condensing)	5...95 %
IP protection category to IEC 60529	IP 20
For mounting on support rails	Yes
Current measurement inputs	8 (2x4) 2 systems – L1, L2, L3, N Individual channels
Measurement by way of low-power current transformer (secondary voltage)	0...0.4 V
Fundamental frequency	40...70 Hz
Harmonic	1...15
Packs of	1 pc(s).
Net weight	0.29 kg
Gross weight	0.295 kg

# Features

---

Customs tariff number	85389099
Product description	SV Current measurement module REM 800-CT-8-LP for secondary current converters

---

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------