

# Rittal – The System.

Faster – better – everywhere.



## PK 9500.000

## Polycarbonate enclosures PK

State: 23.08.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9500.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

Model No.	PK 9500.000
Design	PK enclosure with solid cover
Product description	Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

# Features

Dimensions	Width: 65 mm Height: 65 mm Depth: 57 mm
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	12 pc(s).
Net weight	1.092
Gross weight	1.295
Customs tariff number	94037000
EAN	4028177138933
ETIM 9	EC000261
ECLASS 8.0	27180101

# Approvals

Approvals	C-UL DNV-GL UL UL + C-UL (listed)
Explanations	Declaration of conformity

# Tender text

Polycarbonate Housings without knockouts

Polycarbonate enclosure with solid cover without knockouts  
Enclosure: Fibreglass-reinforced polycarbonate  
without knockouts for cable entry  
Cover: Fibreglass-reinforced polycarbonate  
all-round foamed-in PU seal

Cover screws: Polyamide

Insulating bungs: Polyethylene

Supply includes: Cover screws

Insulating bungs for wall mounting screws

Accessories: Wall mounting bracket

Protection category to IEC 60 529: IP 66

Protection category NEMA: NEMA 4X

Colour: similar to RAL 7035

Dimensions (W x H x T): 65 x 65 x 57 mm