

# Rittal – The System.

Faster – better – everywhere.



## SV 9635.300 Component adaptor

State: 26.06.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.300 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

## Features

Model No.	SV 9635.300
Design	With integral fuse holder
Function principle	For mechanical attachment and direct contacting of electrical equipment on the board
Material	Polyamide Fire protection corresponding to UL 94
Colour	RAL 7035
Note	The technical data may vary for UL applications
Rated current max.	16 A
Rated operating voltage	690 V (AC) 600 V (DC)
Number of poles	3-pole
For fuse type (class)	CC
Electrical ratings UL	Rated operating voltage (max.) UL: 600 V AC
Connection cables (AWG)	AWG 14
Length of connection cable	125 mm
Support rails Qty/height	1 / 10 mm
Support rail type	static
Dimensions	Width: 22.5 mm Height: 160 mm Depth: 80 mm
Packs of	1 pc(s).
Net weight	0.124 kg
Gross weight	0.134 kg

# Features

---

Copper weight (kg per piece)	0.02
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Component adaptor, 16 A, 690 V (AC), 600 V (DC), 3-pole, for fuse 10x38 mm/Class CC, connection cable AWG 14 (L: 125 mm), WH: 22,5x160 mm

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK