



# SV 9635.400 - Motor controller 3-pole

For controlling motors as direct or reversing starters with integral over-ride protection

## Features

|                                |  |
|--------------------------------|--|
| Model No.                      | SV 9635.400  |
| Function principle             | For controlling motors as direct or reversing starters with integral over-ride protection<br>The hybrid technology used facilitates frequent switching by semi-conductors with zero wear<br>During operation, mechanical contacts ensure a low heat loss<br>Space-saving configuration thanks to the minimal build width |
| Material                       | Polyamide<br>Fire protection corresponding to UL 94-V0   |
| Colour                         | RAL 7035   |
| Heat loss max.                 | 2.8 W  |
| Rated operating voltage        | 500 V (AC), 3~, 50 Hz/60 Hz  |
| Rated current max.             | 0.6 A  |
| Note                           | The technical data may vary for UL applications  |
| Dimensions                     | Width: 22.5 mm<br>Height: 160 mm<br>Depth: 114 mm  |
| Connection of round conductors | 0.14 - 2.5 mm <sup>2</sup>   |
| Adjustable current monitoring  | 0.075 - 0.6 A  |
| Packs of                       | 1 pc(s).   |
| Net weight                     | 0.38 kg  |
| Gross weight                   | 0.389 kg   |
| Customs tariff number          | 85371091   |
| ETIM 9                         | EC002572   |
| ECLASS 8.0                     | 27370804   |

# Features

---

|                     |  |
|---------------------|--|
| Product description | SV Motor controller, 0,6 A, 500 V, 50/60 Hz, 3-pole, round conductor connection 0,14-2,5 mm <sup>2</sup> , WH: 22,5x160 mm |
|---------------------|--|

# Approvals

---

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|