

Rittal – The System.

Faster – better – everywhere.



TS 8806.750

Baying systems TS 8

State: 04.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8806.750 - Baying systems TS 8 EMC enclosures

The large enclosures in the TS 8 series offer a good level of shielding across a broad frequency range, even in the standard version. For increased EMC requirements, Rittal's TS 8 enclosure is also available in a high RF attenuation version.

Features

Model No.	TS 8806.750
Product description	The large enclosures in the TS 8 series offer a good level of shielding across a broad frequency range, even in the standard version. For increased EMC requirements, Rittal offers the TS 8 enclosure in a version certified by the VDE with high RF attenuation.
Product modification	<p>Покрытие листовой стали изменено с алюминий-цинк на цинк-магний.</p> <p>The aluminium zinc coating of sheet steel has been changed to a zinc magnesium coating.</p> <p>Преимущества: улучшенная пластичность, оптимальная защита от коррозии, единый внешний вид.</p> <p>The benefits are improved forming qualities, an optimised corrosion behaviour and a uniform look.</p>
Material	<p>Enclosure frame: Sheet steel with zinc magnesium coating, 1.5 mm</p> <p>Roof: Sheet steel with zinc magnesium coating, 1.5 mm</p> <p>Door: Sheet steel with zinc magnesium coating, 2.0 mm</p> <p>Rear panel: Sheet steel with zinc magnesium coating, 1.5 mm</p> <p>Gland plates: Sheet steel, 1.5 mm</p> <p>Mounting plate: Sheet steel, 3.0 mm</p>
Surface finish	<p>Enclosure frame: Uncoated</p> <p>Door, rear panel and roof: Spray-finished on the outside and paint-free on the inside</p> <p>Gland plates: Zinc-plated</p> <p>Mounting plate: Zinc-plated</p>
Colour	RAL 7035

Features

Supply includes	Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Rear panel Roof plate Gland plates Mounting plate 4 eyebolts Lock: 3 mm double-bit 2 TS punched rails 18 x 38 mm 2 support strips fitted in the enclosure depth
Protection category to IEC 60 529	IP 54
Protection category NEMA	NEMA 1
Type rating to UL 50E	Type 1
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 600 mm
Note	For bayed enclosures, the EMC baying seal is required
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	121.8
Gross weight	126.8
EAN	4028177475731
ECLASS 8.0	27180101

Approvals

Approvals	UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK