

# Rittal – The System.

Faster – better – everywhere.



## AX 1006.000

## Basic enclosure AX, stainless steel

State: 14/05/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 1006.000 - Basic enclosure AX, stainless steel

The robust stainless steel enclosure features an integral locator system, enabling fast, easy, reliable and extensive system configuration with no drilling required.



## Features

|                                   |  |
|-----------------------------------|--|
| Model No.                         | AX 1006.000  |
| Material                          | Enclosure: Stainless steel<br>Door: Stainless steel, all-round foamed-in PU seal<br>Mounting plate: Sheet steel<br>Stainless steel 1.4301 (AISI 304) |
| Surface finish                    | Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm<br>Mounting plate: Zinc-plated  |
| Supply includes                   | Enclosure with door(s), opening angle 130°<br>Mounting plate<br>Lock: 3 mm double-bit  |
| Protection category NEMA          | NEMA 1<br>NEMA 3R<br>NEMA 4<br>NEMA 4X<br>NEMA 12  |
| Protection category to IEC 60 529 | IP 66  |
| Type rating to UL 50E             | Type 1<br>Type 3R<br>Type 4<br>Type 4X<br>Type 12  |

# Features

---

|                                      |  |
|--------------------------------------|--|
| IK Code                              | IK10   |
| Dimensions                           | Width: 380 mm<br>Height: 380 mm<br>Depth: 210 mm   |
| Material thickness - door            | 1.5 mm   |
| Material thickness - enclosure       | 1.25 mm  |
| Material thickness of mounting plate | 2 mm   |
| Dimensions mounting plate (W x H)    | 330 mm x 355 mm  |
| Number of doors                      | 1  |
| Lock                                 | Lock version: Cam<br>Number of locks: 1<br>Lock insert: 3 mm double-bit<br>Material lock: Die-cast zinc                |
| Basic material                       | Stainless steel 1.4301 (AISI 304)  |
| Packs of                             | 1 pc(s).   |
| Net weight                           | 9 kg   |
| Gross weight                         | 9.115 kg   |
| Customs tariff number                | 94032080   |
| ETIM 9                               | EC000261   |
| ETIM 8                               | EC000261   |
| ECLASS 8.0                           | 27180101   |
| Product description                  | AX Compact enclosure, WHD: 380x380x210 mm, stainless steel 1.4301, with mounting plate, single-door, with one cam lock |

# Approvals

---

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | Bureau Veritas<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>PCF-declaration                   |

---

## Tender text

Enclosure (compact enclosure, stainless steel)

Enclosure with door:

Stable stainless steel construction

consisting of body folded from a single piece and welded,  
with protection channel all-round door opening,  
solid rear panel with knockouts for attaching  
wall mounting brackets.

Door with foamed-in PU seal,  
screw-fastened hinges.

Right-hand hinge may be swapped to the left,  
130° opening angle to VDI,

Earthing bolt, integral enclosure bosses for interior installation,  
cam lock with double-bit insert to DIN 43668

Mounting plate: With machined keyholes for earthing,  
with imprinted scale, attached with Limbach nuts.

QR code:

QR code printed on body, cover and rating plate  
for clear identification and easy retrieval of relevant  
product information and documentation,  
and for clear traceability of the individual parts.

Accessories: Mini-comfort handle, lock inserts,  
wall mounting bracket, earth straps,  
wiring plan pockets, door stay, viewing window,  
operating panels, fan-and-filter units, heaters,  
swing frame, protective roof

Material:

Enclosure, door: Stainless steel 1.4301 (AISI 304)

Mounting plate: Sheet steel, zinc-plated

Enclosure and door surface finish:

Brushed, grain size 400

Protection category to IEC 60 529: IP 66

Protection category to UL 508A: Type 4X

Dimensions (W x H x D): 380x380x210 mm

Dimensions mounting plate (W x H): 330 x 355 mm