

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.525

## RiLineX CB component adaptor

State: 31.08.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.525 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 400 A) for 60 mm busbar systems. The device width is 140 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



## Features

Model No.	RX 9360.525
Design	Easy Fix
Benefits	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Supply includes	3 terminal covers
IP protection category to IEC 60 529	IP 2XB
Rated current max.	400 A
Rated current (UL)	400 A

# Features

Rated impulse withstand voltage U <sub>imp</sub>	12 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1,000 V
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
To fit manufacturer (model)	ABB (S5 400, S5, T5, XT5, FG400, FG630) Chint (NM8N-400, NM8N-630, NXM-400S, NXM-630S, NXMS-400, NXMS-630) Eaton (NZM3) Fuji Electric (BW400_-3) Hager (X630) Hyundai Electric (400AF, 400, 630AF) LS Electric (400AF, TS400, TS630) Mitsubishi (NF400-SW, NF630-SW) OEZ (BH630) Rockwell (140G-K0F3-D40, 140G-M0F3-D63) Schneider (NSX400, NSX630) Schrack (MC3) Siemens (3VA23, 3VA24) Terasaki (S400, E630, S630)
To fit busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10

# Features

Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 140 mm Height: 325 mm
Packs of	1 pc(s).
Net weight	4
Gross weight	4.298
Copper weight (kg per piece)	1.652
Customs tariff number	85369095
EAN	4028177997127
ETIM 9	EC001531

# Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------