

Rittal – The System.

Faster – better – everywhere.



KL 1522.010 Terminal boxes KL

State: 30/01/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1522.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

Features

Model No.	KL 1522.010
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Enclosure and cover: Brushed, grain 180
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 300 mm Height: 150 mm Depth: 80 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Lock	Number of locks: 4
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).
Net weight	1.673
Gross weight	1.94
Customs tariff number	84879090
EAN	4028177008465
E-Number Sweden	E3404364
ETIM 9	EC000261
ETIM 8	EC000261

Features

ECLASS 8.0

27180101

Approvals

Approvals

Bureau Veritas
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK

Tender text

Stainless steel terminal box without gland plate,
protection cat. IP 66

Enclosure:

of 1.25 mm stainless steel 1.4301 (AISI 304), folded
and welded from a single piece, with all-round
protection channel on the cover aperture. Cover of 1.25
mm stainless steel, sealed, with foamed-in special
cover seal, facilities for connecting PE conductors in
the cover and box, profile strips on both internal
sides with mounting holes. Special plastic bush guards
against accidental loss of the cover screws and
provides screwdriver guidance.

Accessories:

quick-release fastener, cover retainer, plastic cable
gland plate, cover hinges, mounting plate

Surface finish:

brushed

Dimensions (W x H x D): 300 x 150 x 80 mm