

Rittal – The System.

Faster – better – everywhere.



RX 9360.802

RiLineX bus-mounting fuse base

State: 05.10.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.802 - RiLineX bus-mounting fuse base

RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With optical LED fuse monitoring. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm² at an angle of 45° allows easier conductor connection. The device is suitable for tool-free, snap-on mounting and features semi-automatic busbar adjustment for 5 and 10 mm.



Features

Model No.	RX 9360.802
Benefits	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact hazard protection without any additional accessories (such as screw caps)
Material	Polyamide (PA 6) Fire protection corresponding to UL 94-V0
Colour	RAL 35745 RAL 9005
Supply includes	4 bus-mounting fuse bases 12 reducers for D 01 fuses
Cable outlet	Bottom
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60

Features

Dimensions	Width: 27 mm Height: 263 mm Depth: 123.5 mm
Connection of round conductors, fine wire with wire end ferrule	1.5 - 16 mm ²
Connection of round conductors, fine wire with AWG wire end ferrule	AWG 16 - AWG 6
Connection of round conductors, multi-wire	1.5 - 16 mm ²
Connection of round conductors, multi-wire mm ²	AWG 16 - AWG 6
To fit busbars	Height: 5, 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Overvoltage category	4
Contamination level	3
Standards	IEC/DIN EN 60 947-3
Rated insulation voltage	1,000 V
Power dissipation (max.)	5.5 W
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Utilisation category	AC-21B (400 V/100 A)
Fuse inserts	D 02-E 18

Features

Packs of	4 pc(s).
Net weight	1.432
Gross weight	1.437
Copper weight (kg per piece)	0.07
Customs tariff number	85369095
ETIM 9	EC001644

Approvals

Explanations	Declaration of conformity
--------------	---------------------------