


# Rittal – The System.

Faster – better – everywhere.



## RX 9360.825

### RiLineX fuse-switch disconnector

State: 14.02.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

# RX 9360.825 - RiLineX fuse-switch disconnector D-Switch

RiLineX fuse-switch disconnector for 60 mm busbar systems. For use with D 01 (via gauge ring) and D 02 slow fuses (max. 63 A). Also for use with 10 x 38 mm cylindrical fuses via the supplied retaining springs. Integral optical LED fuse monitoring. The switch is lockable in the on and off positions. Spring terminal blocks up to 16 mm<sup>2</sup> at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.



## Features

Model No.	RX 9360.825
Benefits	<p>Reliable contacting of fuse inserts (without screw caps)</p> <p>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)</p> <p>Optical LED fuse monitoring</p> <p>Voltage test through separate opening</p> <p>Maintenance-free tension spring connection up to 16 mm<sup>2</sup></p> <p>Complete contact hazard protection without any additional accessories (such as screw caps)</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p>
General colour	<p>RAL 35745</p> <p>RAL 9005</p>
Supply includes	<p>4 fuse-switch disconnectors</p> <p>12 reducers for D 01 fuses</p>
Rated current max.	63 A

# Features

Cable outlet	Bottom
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 26.8 mm Height: 263 mm Depth: 104.2 mm
Connection of round conductors, fine wire with wire end ferrule	1.5 - 16 mm <sup>2</sup>
Connection of round conductors, fine wire with AWG wire end ferrule	AWG 16 - AWG 6
Connection of round conductors, multi-wire	1.5 - 16 mm <sup>2</sup>
Connection of round conductors, multi-wire mm <sup>2</sup>	AWG 16 - AWG 6
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Overvoltage category	4
Contamination level	3
Standards	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	800 V
Power dissipation (max.)	5.5 W
IP protection category to IEC 60 529	IP 2XB
Operation humidity max.	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Utilisation category	AC-22B (400 V/100 A)

# Features

Fuse inserts	D 02-E 18
Packs of	4 pc(s).
Net weight	1.784
Gross weight	1.792
Copper weight (kg per piece)	0.105
Customs tariff number	85365080
ETIM 9	EC001040

## Approvals

## Explanations Declaration of conformity