## Rittal – The System.

Faster - better - everywhere.





# SV 9676.747 Connection plate

State: 07.11.2025 (Source: rittal.com/ua-en)



## SV 9676.747 - Connection plate for laminated copper bars

For the connection of laminated flat copper bars.

#### **Features**

Model No.	SV 9676.747
Product description	For connecting laminated copper bars to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness.
Material	Connection plate: E-Cu Thrust piece: Stainless steel Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Assembly instruction	The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply.  Busbar claw with threaded insert M10
Number of bars per conductor	2
Mounting dimensions	50 mm
Clamping area for laminated copper bars (W x H)	32 x 20 mm
To fit laminated copper bars	Qty.: 2 with no. of membranes: 10 with membrane width: 32 mm with membrane thickness: 1 mm
Packs of	1 pc(s).
Net weight	0.34
Gross weight	0.346
Copper weight (kg per piece)	0.13
Customs tariff number	73269098
EAN	4028177625556
ETIM 9	EC002270

© Rittal 2025

### **Features**

ECLASS 8.0 27400613

## **Approvals**

Explanations Declaration of conformity

Declaration of conformity UK

© Rittal 2025 3