

# Rittal – The System.

Faster – better – everywhere.



## SK 3130.115

## TopTherm air-air heat exchanger

State: 16/07/2025 (Source: [rittal.com/uae-en](https://www.rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3130.115 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

## Features

|                                     |                                                                                                                                                                                 |
|-------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                           | SK 3130.115                                                                                                                                                                     |
| Design                              | wall-mounted                                                                                                                                                                    |
| Product description                 | Air/air heat exchangers are particularly well-suited to aggressive ambient conditions, because the internal and external air circuits are completely separate from one another. |
| Colour                              | RAL 7035                                                                                                                                                                        |
| Supply includes                     | Complete unit ready for connection<br>Plug-in terminal strip<br>Floating fault signal contact in case of overtemperature<br>Drilling template<br>Assembly parts                 |
| Specific thermal output             | 90 W/K                                                                                                                                                                          |
| Air throughput (unimpeded air flow) | External circuit with 50 Hz: 850 m³/h<br>External circuit with 60 Hz: 945 m³/h<br>Internal circuit at 50 Hz: 850 m³/h<br>Internal circuit at 60 Hz: 945 m³/h                    |
| Rated operating voltage             | 115 V, 1~, 50 Hz/60 Hz                                                                                                                                                          |
| Dimensions                          | Width: 400 mm<br>Height: 1,580 mm<br>Depth: 215 mm                                                                                                                              |
| Pre-fuse                            | Miniature circuit-breaker/fuse: 4 A                                                                                                                                             |
| Temperature control                 | Electronic control with digital display (factory setting +35 °C)                                                                                                                |
| Operating temperature range         | -5 °C...55 °C                                                                                                                                                                   |
| IP protection category to IEC 60529 | Internal circuit IP 54<br>External circuit IP 34                                                                                                                                |

# Features

|                       |               |
|-----------------------|---------------|
| Packs of              | 1 pc(s).      |
| Net weight            | 24.1          |
| Gross weight          | 24.95         |
| Customs tariff number | 84158300      |
| EAN                   | 4028177425125 |
| ETIM 9                | EC002514      |
| ETIM 8                | EC002514      |
| ECLASS 8.0            | 27180711      |

# Approvals

|              |                                                           |
|--------------|-----------------------------------------------------------|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |