


# Rittal – The System.

Faster – better – everywhere.



## VX 9680.608

# Bayed enclosure system VX25

State: 11.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 9680.608 - Bayed enclosure system VX25 Modular enclosure

Baying systems VX, for installation with partial doors and internal separation in a modular design.

## Features

Model No.	VX 9680.608
Material	Sheet steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame Rear panel Gland plates
Protection category to IEC 60 529	Up to IP 54, depending on the panels
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 800 mm
Packs of	1 pc(s).
Net weight	44.7 kg
Gross weight	49.2 kg
PCF per pack (cradle-to-gate)	132.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
ETIM 9	EC000261

# Features

---

ECLASS 8.0	27180101
------------	----------

---

Product description	VX Modular enclosure, WHdepth 600x2000x800 mm, sheet steel
---------------------	--

# Approvals

---

Certificates	Surface finish
--------------	----------------

---

Explanations	Declaration of conformity UK
--------------	------------------------------