### Rittal – The System.

Faster – better – everywhere.





### SK 3201.820

# Modular climate control concept – climate control door VX25

State: 07/12/2025 (Source: rittal.com/uae-en)



## SK 3201.820 - Modular climate control concept – climate control door VX25 for installing cooling modules

Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX.

### **Features**

Model No.	SK 3201.820
Product description	Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX. The climate contro doors fit perfectly with the overall design of the enclosure.
Material	Sheet steel
Colour	RAL 7035
Supply includes	Climate control door without preconfigured cooling module 180° hinges, door opening angle approx. 130°
Note on Model No.	To fit VX enclosures For 1200 mm wide VX enclosures, the existing hinged door may be used, irrespective of the device position (left or right) R/h door hinge
To fit	Enclosure type: VX: = 800 mm: = 1,800 mm
Packs of	1 pc(s).
Net weight	35
Gross weight	37.4
EAN	4028177925748
ETIM 9	EC002510
ETIM 8	EC002510
ECLASS 8.0	27180702

© Rittal 2025 2

### **Approvals**

Certificates	EAC
Explanations	Declaration of conformity - F-gas regulation

### Tender text

SK 3201.820

Modular climate control concept – climate control door VX25 for installing cooling modules

Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX. The climate control doors fit perfectly with the overall design of the enclosure.

Material: Sheet steel Colour: RAL 7035 To fit VX enclosures

Dimensions WxH [mm]: 800x1800

door hinge right

© Rittal 2025