

# Rittal – The System.

Faster – better – everywhere.



## SK 3215.700

# Air/water heat exchangers

State: 28/06/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3215.700 - Air/water heat exchangers wall-mounted HD

Air/water heat exchanger for hygiene-critical production zones in the food and beverage industry – the optimum addition to the Rittal Hygienic Design range. The cleaning-friendly design reduces the risk of contamination and ensures food safety.



## Features

|                     |  |
|---------------------|--|
| Model No.           | SK 3215.700  |
| Design              | Water-carrying parts, copper/brass (Cu/CuZn)   |
| Product description | Air/water heat exchanger for hygiene-critical production zones in the food and beverage industry – the optimum addition to the Rittal Hygienic Design range. The cleaning-friendly design reduces the risk of contamination and ensures food safety.                               |
| Benefits            | Easy-to-clean, hygienic design<br>A roof tilt of 30° prevents objects from being deposited on it, and allows liquids to run off quickly<br>All-round external, replaceable silicone seal prevents the accumulation of dirt between the enclosure and the air-water heat exchanger. |
| Material            | Enclosure: Stainless steel 1.4301 (AISI 304)   |
| Surface finish      | Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm  |
| Supply includes     | Fully wired ready for connection<br>Drilling template<br>Sealing and assembly parts  |

# Features

|  |  |
|--|--|
| Total cooling output                     | L 35 W 10 at 200 l/h: 1 kW<br>L 35 W 10 at 400 l/h: 1.2 kW   |
| Rated operating voltage                  | 230 V, 1~, 50 Hz/60 Hz   |
| Power consumption Pel                    | At 50 Hz: 77 W<br>At 60 Hz: 104 W  |
| Rated current max.                       | At 50 Hz: 0.38 A<br>At 60 Hz: 0.47 A   |
| Permissible operating pressure (p. max.) | 1: 10 bar  |
| Duty cycle                               | 100 %  |
| Cooling medium                           | Water (see Internet for specifications)  |
| Water inlet temperature                  | 1 °C...30 °C   |
| Water connections                        | G 3/8" external thread   |
| Temperature control                      | Thermostat-controlled magnetic valve   |
| Temperature monitoring                   | Internal thermostat, with change-over contact, switching load 16 A, setting range +20 °C ... +60 °C (factory setting +35 °C) |
| Operating temperature range              | 1 °C...70 °C   |
| Dimensions                               | Width: 215 mm<br>Height: 982 mm<br>Depth: 100 mm   |
| Pre-fuse                                 | Miniature circuit-breaker/fuse: 4 A  |
| Setting range                            | 20 °C...60 °C  |
| Protection category to IEC 60 529        | IP 56/59   |
| Protection category NEMA                 | NEMA 4X  |
| Packs of                                 | 1 pc(s).   |
| Net weight                               | 14 kg  |
| Gross weight                             | 14 kg  |
| Customs tariff number                    | 84158300   |
| ETIM 9                                   | EC002515   |

# Features

---

|                     |   |
|---------------------|---|
| ETIM 8              | EC002515  |
| ECLASS 8.0          | 27180712  |
| Product description | SK Air/water heat exchanger, wall-mounted, HD, 1.2 kW, 230 V, 1~, 50/60 Hz, Thermostat-controlled magnetic valve, WHD: 215 x 982 x 100 mm |

---

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | CSA<br>UL + C-UL - FTTA<br>UR + C-UR (recognized) |
| Explanations | Declaration of conformity                         |

---

# Tender text

Air/water heat exchangers wall-mounted HD

Air/water heat exchanger for hygienically sensitive production zones in the food and consumables

industry – the optimum addition to the Rittal Hygienic Design range. The cleaning-friendly design

reduces the risk of contamination and ensures food safety.

Total cooling output L 35 W 10, 200l/h: 1 kW

Total cooling output L 35 W 10, 400l/h: 1,2 kW

Rated operating voltage: 230 V, 1~, 50 Hz/60 Hz

Dimensions WxHxD [mm]: 215x982x100

Material (Enclosure): Stainless steel 1.4301 (AISI 304)

Surface finish (Enclosure): Brushed, grain 400, peak-to-valley height < 0,8 µm

Cooling medium: Water (see instructions for specifications)

Water-carrying parts: Cu/CuZn

Water connections: G 3/8" AG

Permissible operating pressure (p. max.): 1 bar to 10 bar

Temperature control operation (environment): +1°C to +70°C

Temperature control water inlet: +1°C to +30°C

Setting range: +20°C bis +60°C

Temperature monitoring: Internal thermostat, with change-over contact, switching load 16 A, setting

range +20°C ... +60°C (factory setting +35°C)

Temperature control: Thermostat-controlled magnetic valve

Type of connection: Plug-in terminal strip

Miniature circuit-breaker/fuse: 4 A

Power consumption Pel: 77/104 W

Rated current (max.): 0,38/0,47 A

Protection category IP to IEC 60 529: IP 56/59

Protection category NEMA: 4X

Weight: 14 kg