## Rittal – The System.

Faster - better - everywhere.





# SK 3238.718 Blue e+ filter fan

State: 25/11/2025 (Source: rittal.com/uae-en)



#### SK 3238.718 - Blue e+ filter fan

Complete fan-and-filter units for tool-free installation in surfaces. Air throughput  $20-1,160~\text{m}^3/\text{h}$ , protection category IP 54 as standard.







#### **Features**

Model No.	SK 3238.718
Design	wall-mounted
Product description	Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure.
Benefits	Maximum air throughput via pleated filter included in the delivered state
	Easy filter changes, thanks to a new opening mechanism on the louvred grille
	Faster installation on the enclosure with optimised detent hooks
	Diagonal fan technology achieves more even and constant
	ventilation of the enclosure, thanks to improved pressure stability Tool-free assembly
Material	Plastic
Colour	RAL 9005
Supply includes	Complete unit ready to install, including pleated filter
Fan	Axial, shaded pole motor

© Rittal 2025

### Features

Air throughput, unimpeded airflow	At 50 Hz: 53 m³/h
(with chopped-fibre filter)	At 60 Hz: 64 m³/h
Air throughput, unimpeded airflow	At 50 Hz: 63 m³/h
(with pleated filter)	At 60 Hz: 72 m³/h
Air throughput with matching	At 50 Hz: 40 m³/h
outlet filter including chopped-fibre filter	At 60 Hz: 46 m³/h
Air throughput with matching	At 50 Hz: 49 m³/h
outlet filter including pleated filter	At 60 Hz: 55 m³/h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 15.4 W
	At 60 Hz: 15.8 W
Rated current max.	At 50 Hz: 0.2 A
	At 60 Hz: 0.21 A
Dimensions	Width: 148.5 mm
	Height: 148.5 mm
	Depth: 82.5 mm
Installation depth	64 mm
Mounting cut-out	Cut-out width: 124 mm
	Cut-out height: 124 mm
IP protection category to IEC 60	IP 54 with chopped-fibre filter/pleated filter
529	IP 55 with pleated filter and absorber mat
	IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter
	Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-
	proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Note	With the filter fan 3237.XXX, electrical connection is made via two
	single wires (length approx. 300 mm) on the unit, for all other filter
	fans, a screwless spring terminal is used
Operating temperature range	-15 °C55 °C
Storage temperature range	-30 °C70 °C

© Rittal 2025 3

## Features

At 50 Hz: 52 dB(A)
, , , , , , , , , , , , , , , , , , ,
At 60 Hz: 54 dB(A)
1 pc(s).
0.68
84145915
4028177998230
EC000320
EC000320
27180716

## **Approvals**

Approvals	CSA
	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025