Rittal – The System.

Faster – better – everywhere.





SK 3243.710 Blue e+ filter fan

State: 01/12/2025 (Source: rittal.com/uae-en)



SK 3243.710 - Blue e+ filter fan

Complete fan-and-filter units for tool-free installation in surfaces. Air throughput $20-1,160~\text{m}^3/\text{h}$, protection category IP 54 as standard.







Features

Model No.	SK 3243.710
Design	wall-mounted
Product description	Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure.
Benefits	Maximum air throughput via pleated filter included in the delivered state
	Easy filter changes, thanks to a new opening mechanism on the louvred grille
	Faster installation on the enclosure with optimised detent hooks
	Diagonal fan technology achieves more even and constant
	ventilation of the enclosure, thanks to improved pressure stability Tool-free assembly
Material	Plastic
Colour	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Diagonal, 1~ capacitor motor

© Rittal 2025

Features

Air throughput, unimpeded airflow	At 50 Hz: 540 m³/h
(with chopped-fibre filter)	At 60 Hz: 590 m³/h
Air throughput, unimpeded airflow	At 50 Hz: 625 m³/h
(with pleated filter)	At 60 Hz: 716 m³/h
Air throughput with matching	At 50 Hz: 444 m³/h
outlet filter including chopped-fibre filter	At 60 Hz: 498 m³/h
Air throughput with matching	At 50 Hz: 565 m³/h
outlet filter including pleated filter	At 60 Hz: 645 m³/h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 78.7 W
	At 60 Hz: 102.8 W
Rated current max.	At 50 Hz: 0.81 A
	At 60 Hz: 0.9 A
Dimensions	Width: 323 mm
	Height: 323 mm
	Depth: 144.5 mm
Installation depth	124 mm
Mounting cut-out	Cut-out width: 292 mm
•	Cut-out height: 292 mm
IP protection category to IEC 60	IP 54 with chopped-fibre filter/pleated filter
529	IP 55 with pleated filter and absorber mat
	IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter
	Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-
	proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Note	With the filter fan 3237.XXX, electrical connection is made via two
	single wires (length approx. 300 mm) on the unit, for all other filter
	fans, a screwless spring terminal is used
Operating temperature range	-30 °C55 °C
Storage temperature range	-30 °C70 °C

© Rittal 2025 3

Features

At 50 Hz: 62 dB(A)
At 60 Hz: 65 dB(A)
1 pc(s).
4.1
4.292
84145915
4028177997967
EC000320
EC000320
27180716

Approvals

Approvals	CSA
	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025