

# Rittal – The System.

Faster – better – everywhere.



## SK 3303.518

# TopTherm wall-mounted cooling unit Blue e, UL Type 3R/4

State: 02/04/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3303.518 - TopTherm wall-mounted cooling unit

## Blue e, UL Type 3R/4 0.5 - 2.5 kW

Energy-efficient Blue e wall-mounted cooling units in output categories 500 W to 2,500 W with integral e-Comfort controller and electric condensate evaporation (from 1000 W) as standard, protection category UL Type 3R/4, 12.



## Features

|                     |   |
|---------------------|---|
| Model No.           | SK 3303.518   |
| Design              | wall-mounted  |
| Product description | Energy-efficient Blue e wall-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. Protection category UL Type 3R/4, 12.        |
| Benefits            | Suitable for outdoor siting<br>Blue e technology<br>May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller |
| Material            | Sheet steel   |
| Colour              | RAL 7035  |
| Supply includes     | Condenser with hydrophobic RiNano coating<br>Fully wired ready for connection (plug-in terminal strip)<br>Drilling template<br>Assembly parts                                       |

# Features

|  |   |
|--|---|
| Total cooling output to DIN EN 14511           | Cooling output L35 L35/60 Hz: 0.5 kW<br>Cooling output L35 L50/60 Hz: 0.28 kW   |
| Rated operating voltage                        | 115 V, 1~, 60 Hz  |
| Rated current max.                             | At 60 Hz: 5.7 A   |
| Start-up current max.                          | At 60 Hz: 11.5 A  |
| Air throughput (unimpeded air flow)            | External circuit: 345 m <sup>3</sup> /h<br>Internal circuit: 280 m <sup>3</sup> /h  |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 1.3<br>Refrigeration factor L35 L35 (EER) 60 Hz: 1.35   |
| Design   | wall-mounted  |
| Dimensions                                     | Width: 285 mm<br>Height: 620 mm<br>Depth: 298 mm  |
| Protection category to IEC 60 529              | External circuit IP 34<br>Internal circuit IP 56  |
| Protection category NEMA                       | UL Type 3R<br>UL Type 4<br>UL Type 12   |
| Refrigerant/cooling medium                     | Refrigerant: R-513A<br>Quantity: 0.19 kg<br>Global Warming Potential (GWP): 631<br>CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.12 t |
| Temperature control                            | e-Comfort controller (factory setting +35 °C)   |
| Operating temperature range                    | -20 °C...50 °C  |
| Operating temperature max @60 Hz               | 50 °C   |
| Operating temperature                          | Compressor cooling mode from +10 °C ambient temperature. Only the internal fan is active in the temperature range -20 °C to +10 °C.       |
| Storage temperature range                      | -40 °C...70 °C  |
| Setting range                                  | 20 °C...50 °C   |
| Power consumption Pel                          | Power consumption L35 L35/60 Hz: 0.37 kW<br>Power consumption L35 L50/60 Hz: 0.45 kW  |

# Features

---

|  |   |
|--|---|
| Permissible operating pressure (p. max.) | 28 bar  |
| Pre-fuse                                 | Miniature circuit-breaker/fuse: 10 A  |
| Note on Model No.                        | without integral condensate evaporation   |
| Packs of                                 | 1 pc(s).  |
| Net weight                               | 30.5 kg   |
| Gross weight                             | 36.5 kg   |
| Customs tariff number                    | 84158200  |
| ETIM 9                                   | EC000855  |
| ETIM 8                                   | EC000855  |
| ECLASS 8.0                               | 27180704  |
| Product description                      | SK cooling unit Blue e, wall-mounted, UL Type 3R/4,, 0.55 kW, 115 V, 1~, 60 Hz,, Sheet steel,, WHD: 285 x 620 x 298 mm, |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | C-UL<br>UL + C-UL (listed)<br>UL + C-UL - FTTA  |
| Explanations | Declaration of conformity<br>Declaration of conformity - F-gas regulation<br>Declaration of conformity UK |