


Rittal – The System.

Faster – better – everywhere.



HD 2410.111 Cable gland HD

State: 12/02/2026 (Source: rittal.com/uae-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

HD 2410.111 - Cable gland HD

More compact design and the lock nut is included with the supply.



Features

Model No.	HD 2410.111
Design	EMC
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Lock nut
Dimensions	Thread: M16 x 1.5
For cable diameters	5 - 10 mm
Operating temperature range	-20 °C...100 °C

Features

IP protection category to IEC 60
529 IP69 / IPX8 (5 bar, 30 min)

Packs of 5 pc(s).

Net weight 0.2

Gross weight 0.206

Customs tariff number 73072980

EAN 4028177928671

ETIM 9 EC000441

ETIM 8 EC000441

ECLASS 8.0 27149109

Approvals

Approvals UR + C-UR (recognized)
VDE