


Rittal – The System.

Faster – better – everywhere.



SK 3312.083 Rear adaptor

State: 04/03/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3312.083 - Rear adaptor for LCP Inline CW

May be used to close the gap that emerges when installing an LCP Inline.

Features

Model No.	SK 3312.083
Product description	May be positioned to the rear of the set forward LCP Inline CW to close the existing gap to the rear section.
Material	Sheet steel, spray-finished
Colour	RAL 9005
Supply includes	Adaptor With roof plate Assembly parts
Dimensions	Width: 300 mm Height: 2,000 mm Depth: 200 mm
To fit	Enclosure type: VX IT
Packs of	1 pc(s).
Net weight	19 kg
Gross weight	22 kg
Customs tariff number	84159000
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK rear adaptor for depth compensation, ICP Inline CW, based on VX IT, WHD: 300 x 2000 x 200 mm, sheet steel, spray finished, RAL 7035

Tender text

Rear adaptor, 3312.083 for LCP's CW Inline Protruding SK
3313.530/560/570

Height: 2000 mm

Rear adaptor:

For optimum air routing and energy efficient operation of the LCP Inline Protruding units, they protrude 200 mm in front of the server racks.

To fill the gap in the rear section, the adaptor is screwed-fastened onto the rear of the LCP to create a uniform view and efficient air flow.

Rear adaptor, supply includes:

Adaptor frame with roof plate, incl. assembly parts

Dimensions WHD: 300 x 2000 x 200 mm

Colour RAL 9005