


# Rittal – The System.

Faster – better – everywhere.



## FT 2731.010 Viewing window

State: 08/04/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2731.010 - Viewing window for AX

For external mounting on AX enclosures instead of a door and on surfaces.



## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | FT 2731.010   |
| Design                            | 30 section  |
| Product description               | For external mounting on AX enclosures instead of a door and on surfaces. |
| Material                          | Frame: Aluminium, natural anodised.<br>Glass panel: Acrylic               |
| Supply includes                   | Plastic handle with lock insert no. 3524 E                                |
| Protection category to IEC 60 529 | IP 54   |
| To fit Model No.                  | 1010.000<br>1054.000<br>1060.000<br>1360.000                              |
| To fit                            | Enclosure type: AX<br>Width: = 600 mm<br>Height: = 600 mm                 |
| Dimensions                        | Width: 597 mm<br>Height: 597 mm<br>Depth: 36 mm                           |

# Features

|                                   |   |
|-----------------------------------|---|
| Visible area                      | Viewing window width: 537 mm<br>Viewing window height: 537 mm                             |
| Build depth for components (max.) | 32 mm   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 3.236 kg  |
| Gross weight                      | 3.48 kg   |
| Customs tariff number             | 76101000  |
| ETIM 9                            | EC002527  |
| ETIM 8                            | EC002527  |
| ECLASS 8.0                        | 27182204  |
| Product description               | FT Viewing window, WHD: 597x597x36 mm, for AX enclosures instead of the door and surfaces |