


# Rittal – The System.

Faster – better – everywhere.



## SK 3126.100

## TopTherm air-air heat exchanger

State: 08/08/2025 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3126.100 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | SK 3126.100   |
| Design                              | wall-mounted  |
| Product description                 | Air/air heat exchangers are particularly well-suited to aggressive ambient conditions, because the internal and external air circuits are completely separate from one another. |
| Colour                              | RAL 7035  |
| Supply includes                     | Complete unit ready for connection<br>Plug-in terminal strip<br>Floating fault signal contact in case of overtemperature<br>Drilling template<br>Assembly parts                 |
| Specific thermal output             | 17.5 W/K  |
| Air throughput (unimpeded air flow) | External circuit with 50 Hz: 265 m³/h<br>External circuit with 60 Hz: 315 m³/h<br>Internal circuit at 50 Hz: 265 m³/h<br>Internal circuit at 60 Hz: 315 m³/h                    |
| Rated operating voltage             | 230 V, 1~, 50 Hz/60 Hz  |
| Rated current max.                  | At 50 Hz: 0.22 A<br>At 60 Hz: 0.26 A  |
| Dimensions                          | Width: 280 mm<br>Height: 550 mm<br>Depth: 150 mm  |
| Pre-fuse                            | Miniature circuit-breaker/fuse: 2 A   |
| Temperature control                 | Electronic control with digital display (factory setting +35 °C)  |
| Operating temperature range         | -5 °C...55 °C   |

# Features

|                                     |  |
|-------------------------------------|--|
| IP protection category to IEC 60529 | Internal circuit IP 54<br>External circuit IP 34 |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 8.904  |
| Gross weight                        | 9.373  |
| Customs tariff number               | 84158300   |
| EAN                                 | 4028177388956                                    |
| ETIM 9                              | EC002514   |
| ETIM 8                              | EC002514   |
| ECLASS 8.0                          | 27180711   |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |