

Rittal – The System.

Faster – better – everywhere.



SK 3145.000

Tangential fans for 482.6 mm (19")

State: 22/05/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3145.000 - Tangential fans for 482.6 mm (19") Air throughput 320 m³/h

2 U tangential fan with up to 320 m³/h air throughput. The minimal noise generation of 52 dB makes it suitable for use in office environments.

Features

Model No.	SK 3145.000
Product description	Centrifugal fans for direct installation in the 482.6 mm (19") level have a wide column plus favourable noise characteristics to set them apart from other fans.
Colour	RAL 9005
Supply includes	Fully wired unit ready for connection Filter mat
Speed	2,245 rpm
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 37 W At 60 Hz: 46 W
Rated current max.	At 50 Hz: 0.32 A
Dimensions	Width: 482.6 mm Height: 88 mm Depth: 158 mm
Noise level	At 50 Hz: 52 dB(A) At 60 Hz: 62 dB(A)
Maximum static pressure difference	65 - 70 Pa
Operating temperature range	-10 °C...55 °C
Internal circuit at 50 Hz	320 m ³ /h
Internal circuit at 60 Hz	330 m ³ /h
Packs of	1 pc(s).

Features

Net weight	2.3 kg
Gross weight	2.388 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK Tangential fans for 486. mm (19") installation, 320 m ³ /h, 115 V, 50/60 Hz, WHD: 482.6x88x158 mm

Approvals

Explanations	Declaration of conformity
--------------	---------------------------